


ErgoRib

ErgoRib is a light duty anti-fatigue mat designed for use in a wide variety of dry environments. The mat is manufactured from 9.4mm thick closed-cell vinyl foam and comes with a ribbed surface for added traction and grip. The cushioned effect also offers fantastic leg and back comfort whilst providing a barrier to cold floors. With bevel edges to all sides, the ErgoRib is available in a range of widths for the perfect fit.

Features

- **Typical applications:** Ideal for manufacturing plants, assembly lines, picking and packing workstations, logistics warehouses, industrial and laboratory environments and service counters. ErgoRib is also perfect for kennels, livery enclosures and animal grooming areas where added comfort and floor protection is needed.
- **Material:** Microcellular vinyl.
- **Cleaning:** Wash with cold water and a mild detergent. The use of harsh detergents is not recommended.
- **Sustainability:** REACH compliant.
- **Warranty:** Lifetime.



Suitable for indoor use



Code	Metric	Imperial	Thickness	Weight	Type	Colour
06-0315-1	60cm x 90cm	2' x 3'	9.4mm	1.8kg	Mat	Black
06-0315-3	90cm x 150cm	3' x 5'	9.4mm	4.5kg	Mat	Black
06-0315-4	90cm x 300cm	3' x 10'	9.4mm	8.7kg	Mat	Black
06-0315-2	120cm x 180cm	4' x 6'	9.4mm	6.9kg	Mat	Black
06-0315-5	60cm x 18.3m	2' x 60'	9.4mm	35kg	Roll	Black
06-0315-6	90cm x 18.3m	3' x 60'	9.4mm	53kg	Roll	Black
06-0315-7	120cm x 18.3m	4' x 60'	9.4mm	70kg	Roll	Black

Please note, all Imperial sizes have either been rounded up or down to the nearest whole number

ErgoRib

Technical Specification

Slip resistant:	Great slip resistance to level 2
Anti-fatigue:	Great anti-fatigue properties, resistant to level 2
Wear resistant:	Good wear resistant to level 1, suitable for low to medium footfall
Cut to length:	Yes, mat can be cut to length
Cut to size:	Yes, mat can be cut to bespoke sizes
Disability friendly:	Yes, the mats have ramped edges making them suitable for wheelchair users
Dry area:	Yes
Environment:	Suitable for indoor use
Sustainability:	REACH (Registration, Evaluation, Authorisation and Restrictions of Chemicals)
Cleaning:	Wash with cold water and a mild detergent. The use of harsh detergents is not recommended